



More Comfort for Your Horses

Stalls, Aisles, Walkers, Wash Bays, Trailers, Ramps, Wall Liners and More!!!

Kentucky Horse Park



Top Reasons To Buy Humane Rubber Mats

- Custom design and colors available
- Environmentally friendly
- Over 32 years rubber mat experience
- 12 year limited warranty
- Will not harbor or grow bacteria
- Mats will not roll, buckle, or curl
- Minimizes clean-up time
- Flat bottom finish (no grooves for manure and bedding to work in to)
- Recommended by *Michael Plumb's Horse Journal*



With a variety of sizes, thickness, and top surface designs, you can find a matting solution for any area where traction, cushion, and protection is needed.

More Reasons to Choose Humane


- Easy installation
- Place in new or existing facilities
- Provides more horse comfort
- Reduces bedding costs
- Reduces horse injuries
- Textured surface provides traction
- Absolutely non-absorbent
- Insulates against cold and damp

STRAIGHT EDGE MATS: Available in 3/4", 1/2" and 3/8" thickness with Diamond or Button top design. Standard stocking size is 4 x 6 with custom sizes available. *Button top not available in 3/4".*


INTERLOCKING MATS: Our LOKTUFF interlocking stall mats available in 3/4", 1/2" and 3/8" diamond, also 1/2" and 3/8" button mats. Standard stall sizes are 10 X 10, 10 X 12, and 12 X 12, with custom sizes available.

**We recommend 3/4" mats for stalls*

WASHBAYS: Our 1/2" Button mats provide superb traction for the horse, and person working with the horse in wash stall areas. We recommend using our patented interlocking Wash Stall Mat System, which will prevent your mats from slipping or moving about. Custom sizing available. Anti-bacterial and anti-fungal.



AISLE WAYS: Use 1/2" Diamond interlock mats to cover your Aisle Ways. **Our 1/2" interlock mats come in 5 colors; Emerald, Coral, Midnight, Glacier and Black!!!!*



TRAILERS: Use 1/2" Diamond mats, sizing available for any size trailer floor. Easy installation or removal. Easy to keep clean.

SIDEWALL LINERS: Use 3/8" Diamond or Button mats to protect stall and trailer walls.

ROUND PEN AND CORRAL: Our 3/8" Diamond mats with Grommets. Cover rails to provide safety, privacy, or to stop sand from drifting out of the pen.

FOALING STALLS, BREEDING SHEDS, AND SEMEN COLLECTION AREAS:

(below) Try our 3/4" Interlocking Anti-Fatigue Mats for extra comfort and added traction. The waffle underside of these mats give superior hoof traction for your Stallions during breeding and semen collection, and a softer surface for Mares during foaling. They also provide better traction for the Foal during those first critical hours of standing.



WALKER FLOORS:

(above) Humane now has BIGLOK, exclusive interlocking design, 3/4" thick with larger "teeth" (2 1/4"). (3 times stronger than our regular interlock design) Excellent for use in high-traffic areas!! It has all the same benefits as our regular interlock. Custom sizing, easy installation, same textured surface, and will not roll, buckle or curl.

Stall Mat Installation Instructions

Humane stall mats are easy to install. A diagram is sent with each stall kit that shows you exactly how to position the mats in the stall. Below is our recommendations for trimming and subsurface preparation:

Cutting: Mats are easily cut to fit a size, or around obstructions. We recommend using a utility knife with a straight edge. Scribe the mat several times with the knife until the mat is cut through. For larger jobs, you may want to use a reciprocating sawzall, or have Humane custom cut to size.

Subsurface Preparation: The stall subsurface is important. Humane mats can be placed over concrete, asphalt, wood, or any level well-compacted surface. Clean the existing stall surface of any old bedding. It is not necessary to wash down or dry the stall subsurface. Moisture will not affect Humane mats. An economical alternative to a concrete or asphalt subsurface is **crushed fines**. These are available at rock quarries that crush stone. Depending on the location, commonly found materials are limestone or granite fines, which should not exceed **1/8" in size**. The fines are easy to work with, compact well, provide good drainage, and stand up well to freeze/thaw conditions. Fines should be installed to a depth of **4 to 5 inches**, which may require excavating some of the existing material to maintain current stall elevations. It is important that the fines are well compacted. Use water to soak the material aiding in the compaction process. Once the material has been stabilized and leveled, install your mats. **See steps below for installation using crushed fines:**

Step 1- pour crushed fines and level



Step 2- use 3/4" board (mat thickness) to make sure you have enough fines for stall elevation



Step 3 - soak down and compact the fines



Step 4 - when dry, piece the mats together



Step 5 - finished stall just add a small amount of bedding



Humane Manufacturing, since **1907**, has always prided itself in providing safe, sanitary, durable products that ensure the most comfort. Our mats are made from recycled tire-derived rubber material that is **re-vulcanized** (not glued or held together by fillers). If proper care and protection of your valuable horses is a high priority and you desire an efficient method to keep stalls clean, then you can't afford to be without the benefits of Humane stall mats.



Humane Manufacturing, LLC, 805 Moore St, Baraboo, WI 53913

Phone : 800-369-6263 Fax : 608-356-8338 Web: www.humanemfg.com

Email: info@humanemfg.com

